



借出  
Refer

SPECIFICATION:

1. SHELL: STEEL, ZINC PLATED OR TIN PLATED
2. PIN CONTACT: GOLD PLATED OVER NICKEL
3. INSULATOR: PBT GLASS FIBRE REINFORCED  
UL 94-V0
4. CURRENT RATING: 5 AMP
5. DIELECTRIC STRENGTH: 1000V FOR ONE MINUTE
6. INSULATOR RESISTANCE: 1000M MIN AT 500V DC
7. TEMPERATURE: -55°C - +105°C
8. PACKAGE: W/CLEAR POLYBAG



REV	DESCRIPTION	DATE	ECN NO.
1-1	REVISE CONNECTER	OCT-22-2001	
1-0		NOV-19-2000	

  

DWG NAME:	SUPER THIN G.C		
G. W. NO	AG021ACK-00	CUS. ID:	UV001
CUS. NO	970.41132.1	DWG. NO:	V01-132
SHEET:	1/1	TOLERANCE:	UNIT: mm
		.X .XX ±0.40	DRAW. BY:
		SCALE:	CHECKED:
		1:1	