




FROM : GOOD WAY

C  
D  
E  
F  
G



送檢  
Reference Unit



- SPECIFICATION:
1. SHELL: STEEL, ZINC PLATED OR TIN PLATED
  2. PIN CONTACT: GOLD PLATED OVER NICKEL
  3. INSULATOR: PBT GLASS FIBRE REINFORCED  
UL 94 V0
  4. CURRENT RATING: 5 AMP
  5. DIELECTRIC STRENGTH: 1000V FOR ONE MINUTE
  6. INSULATOR RESISTANCE: 1000M MIN AT 500V DC
  7. TEMPERATURE: -55°C -- +105°C
  8. PACKAGE: W/CLEAR POLYBAG

| 1-0                     |             | OCT-18-2003 |           |
|-------------------------|-------------|-------------|-----------|
| REV                     | DESCRIPTION | DATE        | ECN NO.   |
|                         |             |             |           |
| DWG NAME: SUPER THIN GC |             |             |           |
| G. W. NO:               | AG023AEX-00 | CUS. ID:    | 10V001    |
| CUS. NO:                | 920.41132.3 | DWG. NO:    | 10V1-146  |
| SHEET:                  | 1/1         | TOLERANCE:  | UNIT: mm  |
|                         |             | .X          |           |
|                         |             | XX ±0.40    | DRAW. BY: |
|                         |             | SCALE: 1:1  | CHECKED:  |

886 2 89191865

04/02 '02 14:08 NO.512 12