



Drawings not to scale
All dimensions in mm

SPECIFICATION

SWITCHING DISTANCE	Min. mm	8.0
OPERATING TEMPERATURE	Deg. °C	-20° + 85°
STORAGE TEMPERATURE	Deg. °C	-25° + 85°
CASE MATERIAL		Brass-nickel plated

METAL THREADED MAGNET

PART NUMBER
PTM 12

Rev. No.	Revision Note	Date	Signature
B	WEB SITE	1-10-98	RG



BS5750/ISO 9000
Reg. No. FM 21080