

Alnico Shallow Pot Magnet datasheet

- Alnico 5 magnet material
- Magnetically stable at high temperatures
- Brass spacer
- Zinc plated body
- Diameter ground to H6 tolerance
- Custom designs available
- Max. operating temperature 450°C
- Mild steel pot
- Painted red



Product Information

Product No.	Eclipse Magnetics Product No.	Diameter	Height <i>mm</i>	Hole size (csk)	Screw head size	Weight <i>kg</i>	Pull force
TL16122	826	19	7.5	4.5	M3 csk	0.010	3.0
TL16123	827	28.5	8.5	5.2	M4 csk	0.030	5.0
TL16124	828	38.1	10.35	5.2	M4 csk	0.080	13.0