

# Alnico deep pot magnet datasheet

- Alnico 5 magnet material
- Magnetically stable at high temperatures
- Max. operating temperature 220°C
- Mild steel pot, aluminium spacer.
- Zinc plated body
- Diameter ground to H6 tolerance
- Custom designs available



## Product Information

| Product No. | Eclipse Magnetics Product No. | Diameter<br><i>mm</i> | Height | Thread size | Weight<br><i>kg</i> | Pull force |
|-------------|-------------------------------|-----------------------|--------|-------------|---------------------|------------|
| TL16125     | 829                           | 9.5                   | 15     | M3          | 0.005               | 1          |
| TL16126     | 830                           | 12.7                  | 15.9   | M4          | 0.015               | 2          |
| TL16127     | 831                           | 17.5                  | 16     | M6          | 0.023               | 2.65       |
| TL16128     | 832                           | 20.5                  | 19     | M6          | 0.040               | 4          |
| TL16129     | 833                           | 27                    | 25     | M6          | 0.085               | 6.1        |
| TL16130     | 834                           | 35                    | 30     | M6          | 0.184               | 14.75      |