

# LED Lamps and LED Lampholders

LED Lampholders can be supplied with or without LEDs



## Key Features

- LED lampholders
- Supplied with or without LEDs
- Black or Chrome finish

## Colours and voltages:

Colours: Red, Yellow, Green and Blue LEDs  
(High Intensity is standard. Option of extra super bright).

Voltages: LEDs are available for direct connection to 2.0/2.2V or 12Vdc

For other voltages contact sales.

Terminal	Type	Sealed	Body Colour	LED Colour	Voltage	Panel Cutout	Approval	Dimensions
<b>W</b> LED fitted <b>A</b> LED not fitted <b>L</b> LED & Wires fitted	<b>(W) 1047 OO</b> 	<b>S</b> Sealed	<b>B</b> Black	<b>R</b> Red	<b>1</b> LED Resistor	 6.3  6.3max  T85		 12.7 14.5 +/- 0.36 1.5 Ø7.6
<b>W</b> LED fitted <b>A</b> LED not fitted <b>L</b> LED & Wires fitted	<b>(L) 1048 OO</b> 		— Blank	<b>Y</b> Red	<b>4</b> 6Vdc LED			
<b>W</b> LED fitted <b>A</b> LED not fitted <b>L</b> LED & Wires fitted	<b>(L) 1048 OO</b> 			<b>G</b> Green	<b>5</b> 12Vdc LED			
<b>W</b> LED fitted <b>A</b> LED not fitted <b>L</b> LED & Wires fitted	<b>(L) 1048 OO</b> 			<b>B</b> Blue	<b>6</b> 24Vdc LED	 8.0  5.5max  T85		 10.0 14.5 2.0 Ø9.5
<b>W</b> LED fitted <b>A</b> LED not fitted <b>L</b> LED & Wires fitted	<b>(W) 1050 OO</b> 					 8.0  7.0max  T85		 12.4 16.9 2.9 Ø10.0
<b>W</b> LED fitted <b>L</b> LED & Wires fitted	<b>(L) 1035 OA</b> 					 4.5  0.9-1.6  T85		 4.30 20.0 1.0 200.0 1.50 5.08
<b>W</b> LED fitted <b>L</b> LED & Wires fitted	<b>(L) 1036 OA</b> 					 6.0  0.9-1.6  T85		 5.85 20.0 1.0 200.0 4.0 7.9
<b>W</b> LED fitted <b>L</b> LED & Wires fitted	<b>(L) 1037 OA</b> 					 6.35  0.9-1.6  T85		 6.15 20.0 1.0 200.0 4.0 7.9