



SWITCH OPERATION
Horizontal or Vertical Mounting

Drawings not to scale
All dimensions in mm

SPECIFICATION

SWITCHING VOLTAGE	Max. Vac	60
SWITCHING CURRENT	Max. A	0.25
SWITCHING CAPACITY	Max. VA	3
CONTACT RESISTANCE	Max. mΩ	1000
DIFFERENTIAL ANGLE	Max. Deg.°	16
OPERATING TEMPERATURE	Deg. °C	-20° +70°
STORAGE TEMPERATURE	Deg. °C	-25° +70°
CASE MATERIAL		Blue Polystyrene
FEATURES		Non-toxic moving contact

TILT SWITCH ASSEMBLIES

PART NUMBER
TSW 30/60

Rev. No.	Revision Note	Date	Signature
C	1998 Catalogue Page 20	1-4-98	RG



BS5750/ISO 9000
Reg. No. FM 21080