

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0391002003](#)
Status: **Active**
Overview: Eurostyle™ Two-Screw Barrier Strips
Description: 10.00mm Pitch Beau™ Eurostyle™ Two-Screw Terminal Strips, 3 Circuits

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Terminal Blocks
Series	39100
Application	Wire-to-Wire
Component Type	One Piece
Overview	Eurostyle™ Two-Screw Barrier Strips
Product Name	Eurostyle™ Two Screw
Type	Barrier Strip
UPC	78172545152

Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	White
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Stainless Steel
Material - Resin	Nylon
Number of Rows	2
Orientation	Vertical
PCB Retention	Yes
Panel Mount	Mounting Holes Between Circuit
Pitch - Mating Interface	10.00mm
Pitch - Termination Interface	10.00mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	10, 12, 14, 16, 18

Electrical


Current - Maximum per Contact	30.0A
Voltage - Maximum	600V

Material Info

Old Part Number	M800-02-03-5-M1
-----------------	-----------------

Reference - Drawing Numbers

Sales Drawing	SD-39100-013
---------------	--------------



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

Search Parts in this Series

[39100 Series](#)