

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530242](#)
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Super-Safeway® Fixed Mount Industrial GFCI, Permanent Mount, Multi Phase, Manual Reset, Flying Leads, 30A, 120/208V 3 Phase, 0.61m (2.0') Lead Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E66308

General

Product Family Power Distribution
 Series [130153](#)
 Enclosure Rating NEMA 6P
 GFCI Reset Manual
 Mounting Style Permanent
 Open Neutral Relay Yes
 Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
 Product Name Super-Safeway™
 Receptacle Type N/A
 Type GFCI Industrial Duty, Multi-Phase
 UPC 78172542943
 Woodhead Yes

Physical

Cord Diameter N/A
 Cord Grip Body Size N/A
 Cord Length 0.61m (2.0')
 Feed-Thru No
 Flip Lid No
 Material - Housing Nylon
 Number of Receptacles 0
 Packaging Type Carton

Electrical

Cord Type N/A
 Current - Maximum per Contact 30.0A
 GFCI Yes-In-line
 Ground Continuity Monitor No
 NEMA Configuration N/A
 Voltage - Maximum 120V / 208V / 3 Phase

Material Info

Old Part Number 30053-2M5F

Reference - Drawing Numbers

Sales Drawing SD-130153-039



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

Search Parts in this Series

[130153 Series](#)