

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190380004

Status:

Active

Overview:

Snap Plugs and Receptacles

Description:

InsulKrimp™ Snap Plug Receptacle for 18-22 AWG Wire, PVC, Fits Male Plug Diameter 4.57mm

Documents:

3D Model

Product Specification PS-19902-013 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-19902-011 (PDF)

Agency Certification

CSA

LR18689

UL

E152602

General

Product Family

Quick Disconnects

Series

19038

Comments

Fits Male Plug Dia. 4.57mm

Crimp Quality Equipment

Yes

Insulated

Fully

Overview

Snap Plugs and Receptacles

Product Name

InsulKrimp™

Type

Snap Receptacle

UPC

800753048669

Physical

Barrel Type

Closed

Color - Resin

Red

Flammability

94V-0

Gender

Female

Glow-Wire Compliant

No

Insulation

PVC

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

PVC

Net Weight

1.221/g

Orientation

Straight

Packaging Type

Bag

Plating min - Mating

2.540µm

Plating min - Termination

2.540µm

Tab Thickness

N/A

Tab Width

N/A

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

3.25mm max.

Wire Size AWG

18, 20, 22

Electrical

Voltage - Maximum

600V

Material Info

Old Part Number

BRA-2180

Reference - Drawing Numbers

Product Specification

PS-19902-011, PS-19902-013

Sales Drawing

SD-19038-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/108/2014 (17 Dec
2014)

Halogen-Free

Status

Not Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

19038 Series

Application Tooling | FAQ

Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.

Global

Description

Product #

Crimp Head for the

AT-200™ Pneumatic

Hand Tool

Hand Crimp Tool

0640052300

0640012300

This document was generated on 03/03/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION