



Datasheet for part number DBMN5W5SNA197

|   |
|---|
| Our Catalog Part Number: DBMN-5W5S-N-A197                                 |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: COMBO D |

| Product Datasheet               |   |
|---------------------------------|---|
| General                         | Combo D Series: D-Subminiature offering mixed layouts     |
| Wire Gauge Range AWG            | AWG 8-26  |
| Contact Arrangement             | 5W5 (5 empty size 8 cavities)                             |
| Dielectric Withstanding Voltage | 500 VAC at sea level                                      |
| Current Rating Signal Contacts  | 7.5 max   |
| Operating Temperature           | -55°/+125°  |
| Salt Spray Test                 | 20 hours  |
| Shell Material                  | steel   |
| Shell Finish                    | pure tin over nickel                                      |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0                          |
| Insulator Color                 | black   |
| Gender                          | Socket  |
| Contacts                        | delivery without size 8 contacts, please order separately |
| Mounting Method                 | .300? (7.6mm) Standoff, 4-40 Screwlock, Boardlock         |