

General Information

Extended Product Type:	OBOC2000-24VDC
Product ID:	1SNA645051R0400
EAN:	4013614508066
Catalog Description:	OBOC2000-24VDC Optocoupler R600 2A, A1-A2=24VDC, MOS-FET
Long Description:	Screw optocoupler OBOC1000 24vdc : 24vdc input / 5 upto 58vdc output 2A

Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Interface Relays and Optocouplers

Ordering

Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369085
EAN:	4013614508066

Dimensions

Product Net Height:	67.5 mm
Product Net Depth:	70 mm
Product Net Weight:	0.02 kg
Product Net Width:	6 mm

Container Information

Package Level 1 Width:	73 mm
Package Level 1 Height:	71 mm
Package Level 1 Length:	80 mm
Package Level 1 Gross Weight:	0.23 kg
Package Level 1 EAN:	3472596450519
Package Level 1 Units:	10 piece

Technical

Output:	solid-state output
Output Signal:	4.5 ... 58 V DC / 1 mA ... 2 A
Rated Control Supply Voltage (U _s):	24 V DC
Terminal Type:	Screw Terminals
Function:	Boxed optocoupler R600

Environmental

RoHS Status:	Following EU Directive 2011/65/EC
--------------	-----------------------------------

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SVC645000M9000
CSA Certificate:	CSA_254821
cUR Certificate:	cUR_E352056
Data Sheet, Technical Information:	1SVC117001D0200
Declaration of Conformity - CE:	1SVD982016-0000
EAC Certificate:	EAC_RU_C-FR.ME77.B.01634
LR Certificate:	LR_16_20068
RoHS Information:	1SVD982016-4400
UR Certificate:	UR_E352056

Classifications

ETIM 4:	EC001504 - Optocoupler
ETIM 5:	EC001504 - Optocoupler
ETIM 6:	EC001504 - Optocoupler
eClass:	7.0 27371604
UNSPSC:	43172000
Object Classification Code:	K

