

### General Information

Extended Product Type:	JSBR4 24DC
Product ID:	2TLA010002R0000
EAN:	7350024432565
Catalog Description:	JSBR4 24DC Safety relay
Long Description:	Safety relay for two hand device and many other safety products. Power supply 24VDC. Relay outputs 3NO/1NC

### Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Safety Relays  
 Products » Low Voltage Products and Systems » Control Products » Safety Products » Safety Relays

### Ordering

EAN:	7350024432565
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85364110

### Dimensions

Product Net Width:	0.045 m
Product Net Height:	0.074 m
Product Net Depth:	0.120 m
Product Net Weight:	0.350 kg

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	0.131 m
Package Level 1 Height:	0.057 m
Package Level 1 Length:	0.081 m
Package Level 1 Gross Weight:	0.335 kg

### Safety Information

Safety Category Acc. to ISO 13849-1:	4
--------------------------------------	---

### Additional Information

Product Main Type:	JSB
Product Name:	Safety Relay
Rated Control Supply Voltage ( $U_s$ ):	24 V DC
Suitable For:	Interlocking switch/Gate/Hatch, Safety mats, Contact strips, Two-hand control device, Emergency stop, Hold to run/Enabling device, Foot control device, Area supervision

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	2TLC172001C0202_chapter06
Declaration of Conformity - CE:	2TLC172020D0201

### Classifications

E-number:	3860249
ETIM 4:	EC001452 - Two-hand control relay
ETIM 5:	EC001452 - Two-hand control relay
Object Classification Code:	K

