

## General Information

Extended Product Type:	JSTD1-A
Product ID:	2TLA020007R3000
EAN:	7350024460193
Catalog Description:	JSTD1-A Safeball 2m cable
Long Description:	JSTD1-A Safeballs each have 1NO & 1NC independent switches, maximum load of 30VDC - 2A resistive. Ergonomic design with several grip possibilities and low activation force (approx. 2N) and flexible mounting options. Provides highest level of safety for use in two hand control applications when using two Safeballs in conjunction with a JSBR4 safety relay or Pluto Safety PLC. IP67 protection degree, plastic body, 2 meters molded cable.

## Categories

Products » Low Voltage Products and Systems » Control Products » Safety Products » Safety Control Devices

## Ordering

EAN:	7350024460193
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85365011

## Dimensions

Product Net Width:	0.18 m
Product Net Height:	0.17 m
Product Net Depth:	0.18 m
Product Net Weight:	0.38 kg

## Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	0.150 m
Package Level 1 Height:	0.185 m
Package Level 1 Length:	0.150 m
Package Level 1 Gross Weight:	0.460 kg
Package Level 1 EAN:	7350024460193
Package Level 2 Units:	2 piece
Package Level 2 Width:	0.163 m
Package Level 2 Height:	0.235 m
Package Level 2 Length:	0.18 m
Package Level 2 Gross Weight:	0.551 kg
Package Level 2 EAN:	7350024460209

## Safety Information

Performance Level (PL):	Up to e
Safety Category Acc. to ISO 13849-1:	4

## Additional Information

Product Main Type:	JSTD20
Product Name:	Two Hand Safety Control Device

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	2TLC172001C0202_chapter10
Declaration of Conformity - CE:	2TLC172023D0201

## Classifications

ETIM 4:	EC002611 - Control switch
ETIM 5:	EC002611 - Control switch
Object Classification Code:	B

