

General Information

Extended Product Type:	OHYS3RH
Product ID:	1SCA105328R1001
EAN:	6417019412481
Catalog Description:	No Description Available
Long Description:	Selector type handle. Screw mounting, hole distance 36 mm. Indication I-O and ON-OFF. No separate shaft needed. Padlockable with one padlock, IP 54, NEMA 1, red-yellow, OT16...40FT

Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

Ordering

EAN:	6417019412481
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85389099

Dimensions

Product Net Width:	48 mm
Product Net Height:	48 mm
Product Net Depth:	36 mm
Product Net Weight:	0,08 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	50 mm
Package Level 1 Height:	50 mm
Package Level 1 Length:	50 mm
Package Level 1 Gross Weight:	0,08 kg
Package Level 1 EAN:	6417019412481

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
--------------	---

Additional Information

Color:	Red-Yellow
Degree of Protection:	IP54
Handle Type:	Selector
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	10 piece
Product Main Type:	OHYS3R
Product Name:	Handle
Product Type:	OHYS
Suitable For:	OT16-125 & OTDC16-32
Suitable for Product Class:	Switch disconnectors

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
RoHS Information:	1SCC390005D0202

Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

