# OHYS3AH



## **General Information**

**Extended Product Type:** OHYS3AH

Product ID: 1SCA105325R1001 EAN: 6417019412450

**Catalog Description: OHYS3AH Handle** 

Long Description: Selector type handle. Indication I-O and ON-OFF, for shaft diameter 6 mm, door drilling 22.5

mm. IP 54 handles, padlockable with one padlock with bail diameter 5...6.3 mm, NEMA 1, red-yellow, OT16...125F

### **Categories**

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

#### Ordering

EAN:	6417019412450
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85381000

# **Dimensions**

Product Net Width:	48 mm
Product Net Height:	48 mm
Product Net Depth:	41 mm
Product Net Weight:	0.1 kg

### **Container Information**

Package Level 1 Units:	1 piece
Package Level 1 Width:	48 mm
Package Level 1 Height:	41 mm
Package Level 1 Length:	48 mm
Package Level 1 Gross Weight:	0.1 kg
Package Level 1 EAN:	6417019412450

#### **Environmental**

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-07-
	01

# **Additional Information**

Color:	Red-Yellow
Degree of Protection:	IP54
Handle Type:	Selector
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	10 piece
Product Main Type:	OHYS3AH
Product Name:	Handle
Product Type:	OHYS
Suitable For:	OT16 125F
Suitable for Product Class:	Switch disconnectors

# **Certificates and Declarations (Document Number)**

Data Sheet, Technical Information:	1SCC301020C0201
RoHS Information:	1SCC390005D0202

### Classifications

ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	NA

