

General Information

Extended Product Type:	OHBS2AJ
Product ID:	1SCA105213R1001
EAN:	6417019409788
Catalog Description:	OHBS2AJ Handle
Long Description:	Selector type handle. Indication I-O and ON-OFF, for shaft diameter 6 mm, door drilling 22.5 mm. IP 65 handles, padlockable with max. 3 padlocks with bail diameter 5...8 mm, door interlock in ONposition, defeatable, NEMA 1, 3R, 12, black, OT16...125F

Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors Accessories

Ordering

EAN:	6417019409788
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85381000

Dimensions

Product Net Width:	65 mm
Product Net Height:	65 mm
Product Net Depth:	48 mm
Product Net Weight:	0.1 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	65 mm
Package Level 1 Height:	48 mm
Package Level 1 Length:	65 mm
Package Level 1 Gross Weight:	0.1 kg
Package Level 1 EAN:	6417019409788

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-07-01
--------------	--

Additional Information

Color:	Black
Degree of Protection:	IP65
Handle Type:	Selector
IIT Publishing Status:	Level 0 - Information enabled
Order Multiple:	10 piece
Product Main Type:	OHBS2AJ
Product Name:	Handle
Product Type:	OHBS
Suitable For:	OT16 ... 125F
Suitable for Product Class:	Switch disconnectors

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301020C0201
RoHS Information:	1SCC390005D0202

Classifications

E-nummer:	3171316
ETIM 5:	EC000229 - Handle for power circuit breaker
Object Classification Code:	N/A

