

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301370147](#)  
**Status:** **Active**  
**Overview:** [Watertite® Wet-Location Wiring Solutions](#)  
**Description:** Super-Safeway® Multiple Outlet Box, Standard Depth, 2-Sided, Cord Clamp, Box only

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837

**General**

Product Family	Power Distribution
Series	<a href="#">130137</a>
Enclosure Rating	NEMA 4
GFCI Reset	N/A
Mounting Style	Portable
Open Neutral Relay	N/A
Overview	<a href="#">Watertite® Wet-Location Wiring Solutions</a>
Product Literature Order No	987650-7737
Product Name	Super-Safeway™
Receptacle Type	N/A
Type	Multiple Outlet Box
UPC	78678875056
Woodhead	Yes

**Physical**

Cord Diameter	8.26-16.64mm (.325-.655")
Cord Grip Body Size	F4 1"
Cord Length	N/A
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Number of Receptacles	2 - Customer Supplied
Packaging Type	Carton

**Electrical**

Cord Type	N/A
Current - Maximum per Contact	Per Cust. Supplied Receptacle
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	N/A
Voltage - Maximum	Per Cust. Supplied Receptacle

**Material Info**

Engineering Number      3050



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[130137 Series](#)