

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301530126](#)  
**Status:** **Active**  
**Overview:** Ground Fault Circuit Interrupter (GFCI) Products  
**Description:** Super-Safeway® In-Line Industrial GFCI, Portable, Single Phase, Manual Reset, NEMA 5-20 Plug, NEMA 5-20 Receptacle, Watertight, 20A, 120V, 0.61m (2.0') Cord Length

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)  
[Product Literature \(PDF\)](#)

**Agency Certification**

UL      E66308

**General**

Product Family      Power Distribution  
Series      [130153](#)  
Enclosure Rating      NEMA 4X  
GFCI Reset      Manual  
Mounting Style      Portable  
Open Neutral Relay      Yes  
Overview      [Ground Fault Circuit Interrupter \(GFCI\) Products](#)  
Product Literature Order No      987650-7737, 987651-0452  
Product Name      Super-Safeway™  
Receptacle Type      N/A  
Type      GFCI Industrial Duty, Single Phase  
UPC      78678889737  
Woodhead      Yes

**Physical**

Cord Diameter      10.67mm (.420")  
Cord Grip Body Size      Internal Double C-Clamp  
Cord Length      0.61m (2.0')  
Feed-Thru      Yes  
Flip Lid      No  
Material - Housing      Nylon  
Net Weight      910.359g  
Number of Receptacles      1  
Packaging Type      Bag

**Electrical**

Cord Type      12/3 SJEOOW  
Current - Maximum per Contact      20.0A  
GFCI      Yes-In-line  
Ground Continuity Monitor      No  
NEMA Configuration      NEMA 5-20  
Voltage - Maximum      125V

**Material Info**

Engineering Number      20052-1M



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[130153](#) Series