6

N

Switcheraft

Sealed D-Sub



Sealed D-Sub (IP-67)

Features & Benefits:

- Waterproof D-Sub panel connectors and backshell kits meet IP67 rating (when mated).
- Rear mounting panel connectors fit into standard D-Sub holes.
- Connectors are available in solder cup, male and female versions.
- Gold plated contacts are standard.

- Backshell kits available for cable diameters 0.138 - 0.276 in (3.51- 7.01 mm).
- D-Sub solder cup contacts accepts wire ranges from 22-26 AWG.
- Panel mount connector comes with 2 mounting screws.
- RoHS compliant.

Applications:

- Remote or temporary data control centers
- · Manufacturing control equipment
- Marine

- · Instrumentation for field data collection
- · Medical field data collection

D-Sub Panel Mount Series	D-Sub	Gender	Termination Style	Panel
DCP	DB09 = 9 Pin, Standard HD15 = 15 Pin, High Density	M = Male F = Female	SC = Solder Cup	1 = 0.048 - 0.078 in [1.22 - 1.98 mm]

D-Sub Backshell Kit Series	D-Sub	Gender
DCC	DB09 = 9 Pin, Standard HD15 = 15 Pin, High Density	M = Male F = Female

D-Sub Connector Cap Series	Size	Style
DB	S = DB09 or HD15	CAP

Switchcraft[®]


Harsh Environment Connectivity Solutions

Switcheraft com

5555 N. Elston Avenue, Chicago, IL 60630 Phone: 773-792-2700 - Fax: 773-792-2129

Switcheraft

Sealed D-Sub



Electrical Specifications

Current Rating:

Standard D-Sub (9 contact) – 5A High Density D-Sub (15 contact) – 2A

Dielectric Withstanding Voltage: 1000V AC for 1 minute

Contact Resistance: $\leq 25 \text{m}\Omega$

Insulation Resistance: $\geq 500M\Omega$ @ 500V DC

Mechanical Specifications

Life: ≥ 500 Cycles

Environmental Specifications

Operating Temperature: -55°C to +85°C

Thermal Shock: Meets MIL-STD 202G, Method 107G

Condition A

Ratings

IP Rating: IP67 (when mated)

Material Specifications

D-Sub Backshell Kit

Housing, Clamp, & Nut: Thermoplastic, Black

Insulator: Thermoplastic (UL94V-0)
Gasket & Seal: Silicone, Black

Shell: Steel, Tin Plated

Screw: Copper Alloy, Nickel Plated Contact Pins: Copper Alloy, Gold Plated

D-Sub Panel Mount Connector

Flange & Insulator: Thermoplastic (UL94V-0)

Shell: Steel, Tin Plated Epoxy: Epoxy, Black O-Ring: Silicone, Light Blue

Screw: Copper Alloy, Nickel Plated
Contact Pin: Copper Alloy, Gold Plated

D-Sub Connector Cap

Body: Thermoplastic, Black Gasket & O-ring: Silicone, Black Screw: Copper Alloy, Nickel Plated

Chain: Stainless Steel

Switchcraft[®]

Harsh Environment Connectivity Solutions

Switchcraft.com

5555 N. Elston Avenue, Chicago, IL 60630 Phone: 773-792-2700 - Fax: 773-792-2129