

## Steel Rack Panels *PBPS Series*

Also referred to as a Spacer Blank Panel

### Features



- Constructed of 14-gauge steel.
- Fits standard EIA-310-D compliant rails.
- Install in unused rack space to improve both cooling efficiency and prevent air re-circulation.
- Finished in smooth powder paint.
- RoHS Compliant.
- Manufactured in North America.

### Accessories

- Mounting Hardware



### 19 Inch Rack Mounting

Part No. Gloss Black	Part No. Matte Black	Part No. ASA 61 Gray	Part No. Light Gray	Panel Height		Number of Mounting Slots
				Rack Units	Inches	
PBPS19001BK2	PBPS19001BK	PBPS19001GY2	PBPS19001LG2	1U	1.75	4
PBPS19003BK2	PBPS19003BK	PBPS19003GY2	PBPS19003LG2	2U	3.50	4
PBPS19005BK2	PBPS19005BK	PBPS19005GY2	PBPS19005LG2	3U	5.25	4
PBPS19007BK2	PBPS19007BK	PBPS19007GY2	PBPS19007LG2	4U	7.00	4
PBPS19008BK2	-	PBPS19008GY2	PBPS19008LG2	5U	8.75	4
PBPS19010BK2	-	PBPS19010GY2	PBPS19010LG2	6U	10.50	8
PBPS19012BK2	-	PBPS19012GY2	PBPS19012LG2	7U	12.25	8
PBPS19014BK2	-	PBPS19014GY2	PBPS19014LG2	8U	14.00	8
PBPS19015BK2	-	PBPS19015GY2	PBPS19015LG2	9U	15.75	8
PBPS19017BK2	-	PBPS19017GY2	PBPS19017LG2	10U	17.50	8
PBPS19019BK2	-	PBPS19019GY2	PBPS19019LG2	11U	19.25	8
PBPS19021BK2	-	PBPS19021GY2	PBPS19021LG2	12U	21.00	8
PBPS19022BK2	-	PBPS19022GY2	PBPS19022LG2	13U	22.75	8
PBPS19024BK2	-	PBPS19024GY2	PBPS19024LG2	14U	24.50	10
PBPS19026BK2	-	PBPS19026GY2	PBPS19026LG2	15U	26.25	10
PBPS19028BK2	-	PBPS19028GY2	PBPS19028LG2	16U	28.00	12
PBPS19029BK2	-	PBPS19029GY2	PBPS19029LG2	17U	29.75	12
PBPS19031BK2	-	PBPS19031GY2	PBPS19031LG2	18U	31.50	12

### 24 Inch Rack Mounting

Part No. Black	Part No. Light Gray	Panel Height		Number of Mounting Slots
		Rack Units	Units	
PBPS24005BK2	PBPS24005LG2	3U	5.25	4
PBPS24008BK2	PBPS24008LG2	5U	8.75	4
PBPS24017BK2	PBPS24017LG2	10U	17.50	8

*Data subject to change without notice*

© 2016. Hammond Manufacturing Ltd. All rights reserved.