

Rackmount Adjustable Angle Bracket *RAAB Series*

The Rackmount Adjustable Angle Bracket (RAAB) is designed to support the weight of non rack mounted heavy equipment. It is also useful for front-only rack mounted equipment. Available in two depth ranges the RAAB can support up to 200 lbs and can adjust from 24 up to 48 inches in depth.



Features

- Constructed in 16-gauge steel.
- Angles mount to 19 or 23 EIA rack mounting rails.
- Requires two pairs of mounting rails.
- Designed to support equipment such as servers, switch gear as well as computer/server chassis on their side.
- Free-floating design easily adjusts in depth to accommodate different equipment dimensions.
- Two adjustable depth options.
- Sold in pairs.
- Finished in smooth black powder paint.
- Requires mounting hardware.
- Tested to nearly double the suggested load rating of 200 lbs.
- RoHS Compliant.
- Manufactured in North America.

| Part No. | Height | Overall Dimensions | | | Rack Units |
|-------------------|--------|--------------------|-----------|-----------|------------|
| | | Width | Min Depth | Max Depth | |
| RAAB2436BK | 1.72 | 3.14 | 24.00 | 36.00 | 1U |
| RAAB3648BK | 1.72 | 3.14 | 36.00 | 48.00 | 1U |

Data subject to change without notice