

Product data sheet

Characteristics

H362DSWC

SWITCH FUSIBLE HD 60A STNLESS/CR-HI

REC

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Receptacle Switch
Product destination	Plug APJ6485 Crouse-Hinds Arktite
Line Rated Current	60 A
NEMA degree of protection	NEMA 3/3R/4/4X/5/12 stainless steel
Motor power hp	30 hp 480 V AC 50 hp 600 V AC
Disconnecter device type	Fusible disconnect switch
Short-circuit current	≤ 200 kA 10 kA
Device mounting	Surface
Number of poles	3
Phase	3 phases
Electrical connection	Receptacle
Product certifications	UL listed
System Voltage	600 V AC
AWG gauge	AWG 12...AWG 2 (aluminium) AWG 14...AWG 2 (copper)
Wiring configuration	4-wire

Ordering and shipping details

Category	00118 - H&HU SW,W/C-HINDS RECPT-WC
Discount Schedule	DE1
GTIN	00785901076995
Nbr. of units in pkg.	1
Package weight(Lbs)	25
Returnability	N
Country of origin	US

Feb 23, 2017

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1313 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------