



Main

Product or component type	Single Throw Safety Switch
Line Rated Current	200 A
Product certifications	UL listed
NEMA degree of protection	NEMA 3/3R4/4X/12 stainless steel 304
Device composition	None
Disconnecter device type	Fusible disconnect
Short-circuit current	10 kA H or K 200 kA R, J or L
Device mounting	Surface
Number of poles	4
Electrical connection	Lugs
Series name	Heavy duty
System Voltage	600 V AC/DC
AWG gauge	AWG 6...250 kcmil (copper or aluminium)

Ordering and shipping details

Category	00160 - DE1 MISC
Discount Schedule	DE1
GTIN	00785901369578
Nbr. of units in pkg.	1
Package weight(Lbs)	47
Returnability	N
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 0313 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------