

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Single Throw Safety Switch
Line Rated Current	1200 A
Product certifications	UL listed
NEMA degree of protection	NEMA 3R galvanized steel
Device composition	None
Disconnect device type	Fusible disconnect
Short-circuit current	200 kA maximum L
Device mounting	Surface
Number of poles	2
Electrical connection	Lugs
Series name	Heavy duty
System Voltage	600 V AC/DC
AWG gauge	AWG 3/0...750 kcmil (copper or aluminium)

Ordering and shipping details

Category	00054 - H&HU SW,NEMA3R,400-1200A
Discount Schedule	DE1
GTIN	00785901259312
Nbr. of units in pkg.	1
Package weight(Lbs)	359
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1313 - Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------