

Accessories for subracks

Ripac box type plug-in units/installation



Covers

for type I and II box type plug-in units

Without vent slots

For slide-in fastening.

Material:

1.0 mm aluminium, untreated



With vent slots

For screw fastening.

Suitable for the installation of guide rails.

Material:

1.2 mm sheet steel, spray-finished

Colour:

RAL 9006

Unit width	Packs of	Model No. RP	
		with vent slots ¹⁾	without vent slots
Board depth 160 mm			
8 HP	1	–	3687.555
10 HP	1	3687.556	3685.689
12 HP	1	3687.557	3685.690
14 HP	1	3687.558	3685.691
21 HP	1	3687.559	3685.692
28 HP	1	3687.560	3685.693
42 HP	1	3687.561	3685.694
Board depth 220 mm			
8 HP	1	–	3687.562
10 HP	1	3687.563	3685.701
12 HP	1	3687.564	3685.702
14 HP	1	3687.565	3685.703
21 HP	1	3687.566	3685.704
28 HP	1	3687.567	3685.705
42 HP	1	3687.568	3685.706



Also required:

¹⁾ Assembly screws, packs of 100 sets, Model No. RP 3685.289, see page 577.



Covers

for type I und II box type plug-in units

Slide-in, with vent holes (EMC).

Material:

1.0 mm aluminium, untreated

Unit width	Packs of	Model No. RP	
		Board depth	
		160 mm	220 mm
8 HP	1	3687.585	–
10 HP	1	3685.683	3685.695
12 HP	1	3685.684	3685.696
14 HP	1	3685.685	3685.697
21 HP	1	3685.686	3685.698
28 HP	1	3685.687	3685.699
42 HP	1	3685.688	3685.700



Guide rails

for box type plug-in units, see page 512.