



Rear feet

For mounting on the rear of the enclosure.
Dual function:

- Mechanical protection of the connection components.
- Also acts as a cable tidy during transportation.

Material:
PA, self-extinguishing to UL 94-V0

Colour:
RAL 7035

Packs of	Model No. VM
4	3901.000



Earthing set

For connecting the cover plates/gland plates to the side panels with PE conductors.

Supply includes:
Conductor cable green/yellow, 1.5 mm², with washer, flat-pin connector and assembly parts.

Packs of	Model No. RP
4	3900.000



Support stand/carrying handle

To fit Ripac Vario Module 3 U, 4 U and 6 U, adjustable on a 30° pitch pattern.

Material:
Extruded aluminium section/die-cast

Colour:
RAL 7035

Supply includes:
Assembly parts.

Note:
Corner trim for support stands/carrying handles should be ordered separately.

For Ripac Vario-Module	Packs of	Model No. VM
42 HP	1	3981.390
63 HP	1	3981.400
84 HP	1	3981.410

German patent no. 41 10 873

Corner trim for support stand	Packs of	Model No. VM
3 U	2	3981.310
4 U	2	3981.500
6 U	2	3981.510



Acrylic front doors

horizontally hinged
For protection of built-in control components.

Material:
Side parts:
Aluminium, spray-finished in RAL 7035.
Window: Smoked acrylic

Supply includes:
Assembly parts.

U	For Ripac Vario-Module	Packs of	Model No. VM
3	42 HP	1	3981.420
3	63 HP	1	3981.430
3	84 HP	1	3981.440
4	84 HP	1	3981.450
6	84 HP	1	3981.460
7	84 HP	1	3981.470

German patent no. 41 10 872



Front panels/rear panels

To cover the enclosures front and rear.
Also available as a hinged or EMC version.
Model No. see page 538/539.