



Manufacturer Part No: PSM 100A

Features

- Lightweight and compact, ideal for sanding in hard-to-reach areas and for sanding smaller and medium sized surfaces
- Clean working thanks to Microfilter System
- Built-in dust extraction element sucks the dust directly into the Microfilter Box
- Micro hook and loop fastening system
- Two-piece sanding plate for optimum utilisation of the sanding paper
- Delta tip of the sanding paper and of the sanding plate can be effortlessly detached and rotated
- Orbital stroke rate: 26,000 opm
- Oscillating circuit diameter: 1.4mm
- Uses 2-part sanding pads
- Supplied with 3 sanding sheets: 80, 120, 160, Plastic Case

Specifications	PSM 100 A (replaces PSM 80 A)
Power input	100 W
Sanding surface	104cm ²
Orbital stroke rate	26,000 opm
Orbit diameter	1.4mm
Dimensions (length × width × height)	210mm × 105mm × 120 mm
Weight	0.9kg