

# L-50C

## CCD Linear Imager

### HIGHLIGHTS

- Custom logo display area
- Reads high res barcodes
- Reads from LCD screens
- Scan rate 300 scans/sec
- LED aiming

### CUSTOM LOGO DISPLAY



# L-50C

## Basic product specifications

### OPERATING INDICATORS

**CPU:** 32-bit CISC, 96 MHz **VISUAL:** 1 white LED **NON-VISUAL:** Buzzer

### OPERATING KEYS

**ENTRY OPTIONS:** 1 scan key

### COMMUNICATION

**RS232:** D-SUB9 pin (with external power supply) **KEYBOARD WEDGE:** PS/2

**USB:** Ver. 2.0, HID/COM, USB-A connector

### POWER

**VOLTAGE REQUIREMENT:** 6V ± 5% (Keyboard Wedge and RS232) **CURRENT**

**CONSUMPTION:** Max. 165mAh

### BARCODE SCANNER OPTICS

**LIGHT SOURCE:** red LED, 624 nm **SCAN METHOD:** CCD linear image

sensor, 1500 pixels **SCAN RATE:** 300 scans/sec **TRIGGER MODE:** Manual, auto-trigger, stand detection **READING PITCH ANGLE:** -50 to 0°, 0 to +50°

**READING SKEW ANGLE:** -65 to 0°, 0 to +65° **READING TILT ANGLE:** 25°

**CURVATURE:** R>15 mm (EAN8), R>20 mm (EAN13) **MIN. RESOLUTION AT**

**PCS 0.9:** 0.076 mm **MIN. PCS VALUE:** 0.3 **DEPTH OF FIELD AT CODE 39:**

35 - 90 mm / 1.38 - 3.54 in (0.127 mm / 5 mil), 30 - 120 mm / 1.18 - 4.72 in (0.15 mm / 6 mil), 15 - 220 / 0.59 - 8.66 in (0.254 mm / 10 mil), 25 - 350 mm / 0.98 - 13.78 in (0.508 / 20 mil), 40 - 600 mm / 1.57 - 23.62 in (1.0 mm / 39 Mil)

### SUPPORTED SYMBOLOGIES

**BARCODE (1D):** JAN/UPC/EAN incl. add on, Codabar/NW-7, Code 11, Code 39, Code 93, Code 128, GS1-128 (EAN-128), GS1 DataBar (RSS), GS1 DataBar Limited, GS1 DataBar Expanded, Code 11, IATA, Industrial 2of5, Interleaved 2of5, ISBN-ISSN-ISMN, Matrix 2of5, MSI/Plessey, UK/Plessey, S-Code, Telepen, Tri-Optic, UK/Plessey **POSTAL CODE:** Chinese Post Matrix 2of5, Korean Postal Authority code

### DURABILITY

**TEMPERATURE IN OPERATION:** 0 to 50 °C / 32 to 122 °F **TEMPERATURE**

**IN STORAGE:** -20 to 60 °C / -4 to 140 °F **HUMIDITY IN OPERATION:** 5 -

95% (non-condensing) **HUMIDITY IN STORAGE:** 5 - 95% (non-condensing)

**AMBIENT LIGHT IMMUNITY:** Fluorescent 10,000 lx, Direct sun 100,000 lx,

Incandescent 10,000 lx **DROP TEST:** 1.5 m / 5 ft drop onto concrete surface

**VIBRATION TEST:** 10 - 100 Hz with 2G for 1 hour **PROTECTION RATE:** IP 42

### PHYSICAL

**DIMENSIONS (W X H X D):** 75.4 x 169.5 x 121.2 mm / 2.97 x 6.67 x 4.77 in

**DIMENSIONS STAND (W X H X D):** 120 x 294 x 180 mm / 4.72 x 11.57 x 7.09

in (excl. scanner) **CABLE LENGTH:** 2.0 m **WEIGHT BODY:** Ca. 145 g / 5.1 oz

(excl. cable) **WEIGHT STAND:** Ca. 335 g / 11.8 oz **CASE:** ABS/PC, Black or

White

### REGULATORY & SAFETY

**PRODUCT COMPLIANCE:** CE, FCC, VCCI Class B, RoHS, IEC/EN 62471-

1:2006, EN55022, EN55024

### ENCLOSED ITEMS

Power supply 6V/2A (for RS232), Stand

### MODELS

**INTERFACE VERSIONS:** RS232, Keyboard Wedge, USB

