



SCHEMATIC

## MATERIALS:

Center Contact – Gold Plated Beryllium Copper with Teflon insulation.

Resistor Terminator

Dielectric: PTFE

## RATING:

Operating Voltage: 335 VRMS Max.

Operating Temperature: -65°C to +125°C

Nominal Impedance: 50 Ohms

VSWR:

DC – 4 GHz :1.05:1 Max.

4 – 8 GHz :1.10:1 Max.

8 – 12 GHz :1.15:1 Max.

12 – 18 GHz :1.25:1 Max.

Frequency Range: DC to 18.0 GHz

Power: 1 Watt

## ORDERING INFORMATION: Model 4286

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA