

Detailed View

Farnell Order Code: 146-6997

71.35.444 **Vibration Mount, cylindrical /
Inside and Outside Thread**

Lenght 10,0 mm
Material Rubber
Coulor zinc plated
UL-Rating M4
Slot Depths 10,0 mm
Slot Width 4,0 mm
Model In-Outside Thread
Width 10,0 mm
Design Grade of Hardness 55-57°
RoHS compliant

