

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015311092

Status:

Active

Description:

4.80mm Pitch Wire-to-Wire Receptacle Housing, 9 Circuits

Documents:

Drawing (PDF)	Product Specification PS-5025-003 (PDF)
Product Specification PS-5025-001 (PDF)	Packaging Specification SPK-5025-001 (PDF)
Product Specification PS-5025-002 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	5025
Application	Power, Wire-to-Wire
Product Name	N/A
UPC	800753604179

Physical

Circuits (maximum)	9
Color - Resin	Natural
Flammability	94V-2
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	3193.400/mg
Number of Rows	3
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.80mm
Pitch - Termination Interface	4.80mm
Temperature Range - Operating	-40°C to +105°C

Material Info

Engineering Number	5025-09R1
--------------------	-----------

Reference - Drawing Numbers

Packaging Specification	SPK-5025-001
Product Specification	PS-5025-001, PS-5025-002, PS-5025-003
Sales Drawing	SD-5025-09R1

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5025 Series

Mates With

5025 Plug

Use With

5005

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION