


DESTB-1002

2 Pole steatite ceramic high temperature blocks terminal 57a 750v



SPECIFICATION

Number of Poles	2
Body Material	Steatite
Colour	White
Min Conductor Size (Sq mm)	2.5
Max Conductor Size (Sq mm)	16
Min Conductor Size AWG	18
Max Conductor Size AWG	8
Max Current (A)	57
Max Voltage (V)	750
Minimum Temp Rating °C	-40
Max Temp Rating °C	300-350
Pitch (mm)	18.5
Height (mm)	23
Width (mm)	30
Length (mm)	34
Comments	M4 conductor clamping screws, maximum torque=1.2Nm

DISTRIBUTORS

