

# shesto™

## Ultrasonic Cleaning Tanks - Overview

- Available in 2, 3, 6, 9 & 27 litre tanks
- Removes Dirt, Grease, Corrosion - Used for cleaning Electronic & Mechanical parts
- Degas mode - Removes air after solution change, providing maximum cleaning effectiveness
- Delicate mode - Runs at half power providing a less aggressive cleaning action for fragile items
- Full-power mode - Powerful deep clean that will cleanse heavily contaminated items
- Temperature and Timing mode - Allows the user to set both the fluid temperature and duration of the cleaning cycle
- Tank, lid and housing made from stainless steel
- Comprehensive manual included
- All Shesto Tanks include Stainless Steel basket and both UK & EU plugs



We offer a full repair service both inside and outside of the 1 year return to base warranty period. Our team of Electronic Engineers have many years' experience in Ultrasonic cleaner systems, capable of repairing units to component level.

## Shesto Tanks

### Available Models

Internal Tank Dimensions  
in (mm) Bath Lip

Model Number.	Tank Vol.	L	W	H	Heating Power (W)	Frequency (KHz)	Ultrasonic Power (W)
UT8021/EUK*	2 Litre	150	137	100	100	40	100
UT8031/EUK*	3 Litre	240	137	100	100	40	100
UT8061/EUK	6 Litre	300	153	150	300	40	150
UT8091/EUK	9 Litre	300	240	150	300	40	200
UT8271/EUK	27 Litre	495	295	195	500	40	500

\*Drainage taps only available on 6 litre tanks and above



Digital Display



Degas Mode



Timer Control



Baskets Included



Delicate Mode



Drainage Tap\*



Industrial Use



Temperature Control



Shesto Ltd.  
Unit 3 Century Court,  
Tolpits Lane, Watford,  
WD18 9RS

+44(0)208 451 6188  
sales@shesto.co.uk  
www.shesto.com