

2.5mm & 3.5mm JACK PLUGS



JPO-25

2.5mm unscreened Jack Plug. Black plastic body only. Careful soldering assembly required.

Max. cable Ø3.5mm.



P6C

2.5mm and 3.5mm mono unscreened Jack Plug. Allows larger cable use.

P6C-A - 3.5mm model. Cable entry Ø5.3mm

P6C-D - 2.5mm model. Cable entry Ø4.0mm

Also available subject to minimum quantity are models with low profile barrel and strain relief. Refer to Sales.



JPS-35

3.5mm stereo unscreened Jack Plug. Black plastic body only.

JPS-35G. Gold plated version.

Max. cable Ø5mm.

Features

- Low profile barrels available in 2.5mm and 3.5mm.
- Manufactured from solid nickel plated brass.
- Metal cable clamps.
- Incorporate molded plastic insulators.
- Riveted construction.
- Covers are ABS.

Drawings available on request. Contact sales@cliffuk.co.uk

1/4" JACK PLUGS



P1C - 1/4" mono screened Jack Plug. Metal body.
P3C - Stereo version.
Max. cable Ø6.4mm with grommet removed.



P2C - 1/4" mono unscreened Jack Plug. Plastic body available in various standard colors.
P4C - Stereo version.
Max cable Ø6.5mm.




SEP/1C - 1/4" mono screened 90° Jack Plug. Has plated plastic body.
SEP/3C - Stereo version.
Max cable Ø6.4mm



SEP/2C - 1/4" mono unscreened 90° Jack Plug. Plastic body available in various standard colours.
SEP/4C - Stereo version.
Max. cable Ø5.0mm.



SEP/3C Professional - 1/4" stereo screened right angle Jack Plug. Metal body with black plastic cover.
SEP/1C Professional - Mono version.



Jack Leads

We can offer a complete service to design and manufacture custom moulded cable assemblies, including Jack, XLR, DIN, Bantam, DMX and power leads.
Contact sales for more details.

Features

- Rivetted construction.
- Manufactured from solid nickel plated brass.
- Incorporate high temperature Phenolic / PBT insulators.
- Metal bodies made from chrome plated brass.
- Plastic bodies made from ABS.
- All versions fitted with cable clamp.