

156-01601



Article Number: 156-01601

Description: Rotatable Cable Tie and Edge Clip, 8.0" Length, Outside Serrated, PA66HS, Black, 500/bag

Base Data	
Local Order Number	156-01601
Type	CBTO50R
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> <li>• Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.</li> <li>• Edge Clip provides low insertion force and high extraction force ideal for assembly environments.</li> <li>• Cable tie is both rotatable and outside serrated to reduce bundle chafing.</li> </ul>
Quantity Per	bag
Product Description	The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.
Short Description	Rotatable Cable Tie and Edge Clip, 8.0" Length, Outside Serrated, PA66HS, Black, 500/bag
Product Dimensions	
Minimum Tensile Strength (Imperial)	50.0lbs
Minimum Tensile Strength (Metric)	225N
Length L (Imperial)	8.0"
Length L (Metric)	202mm
Length L2 (Imperial)	0.52"
Fixation Method	Edge Clips with tie
Identification Plate Position	none
Length L2 (Metric)	13.2mm
Releasable Closure	No
Variant	Inside Serrated
Width W (Imperial)	0.18"
Width W (Metric)	4.6mm
Cable Tie Width Max. (Imperial)	0.18"

156-01601



Product Dimensions	Cable Tie Width Max. (Metric)	4.6mm
	Width W2 (Imperial)	0.5"
	Width W2 (Metric)	12.0mm
	Height H (Imperial)	0.05"
	Height H (Metric)	1.2mm
	Height H2 (Imperial)	0.6"
	Height H2 (Metric)	15.2mm
	Bundle Diameter Min. (Imperial)	0.08"
	Bundle Diameter Min. (Metric)	2.0mm
	Bundle Diameter Max. (Imperial)	1.9"
	Bundle Diameter Max. (Metric)	47.0mm
	Panel Thickness Max. (Imperial)	0.12"
	Panel Thickness Max. (Metric)	3.0mm
	Panel Thickness Min. (Imperial)	0.04"
	Panel Thickness Min. (Metric)	1.0mm
	Thickness T (Imperial)	0.05"
	Thickness T (Metric)	1.2mm
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
	Material Shortcut	PA66HS
	Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	4.5kg