

166-90269

HellermannTyton

Article Number: 166-90269

Description: HelaGuard Non-Metallic Conduit, Std. Weight, 1.50" Dia, Nylon PA12 Slit, Black, 50 ft/Std. Reel



Base Data	
Local Order Number	166-90269
Type	HG-HISL1500
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> • Very high impact strength; recovers completely if crushed and provides excellent fatigue life. • Highly UV resistant; suitable for use in outdoor applications. • Offered in fine or coarse corrugated pitch. • Offered with or without slit; slit options offer easy access during installation and maintenance.
Quantity Per	reel
Product Description	A standard weight corrugated conduit made of PA12 nylon that offers superior impact resistance, making it ideal for protecting wire and cable bundles in conditions with continual movement or bending. This material is highly resistant to UV light, solvents and oils. Combine with HelaGuard non-metallic fittings to achieve IP66 or greater protection against water, wind and dirt.
Short Description	HelaGuard Non-Metallic Conduit, Std. Weight, 1.50" Dia, Nylon PA12 Slit, Black, 50 ft/Std. Reel
Product Dimensions	
Length L (Imperial)	50.0ft
Length L (Metric)	15.2m
Inner Diameter D (Imperial)	1.86"
Inner Diameter D (metric)	47.2mm
Euro (NW) Size	48mm
Pitch Type	C (Coarse)
Trade Size	1-1/2 "
Outside Diameter D (imperial)	2.15"
Outside Diameter D (metric)	54.5mm
Nominal Diameter (Imperial)	1-1/2"
Nominal Diameter (Metric)	54mm
Inside Bend Radius (Imperial)	2.76"

166-90269



Product Dimensions	Inside Bend Radius (Metric)	70mm
Material and Specifications		
	Material	Polyamide 12 (PA12)
	Material Shortcut	PA12
	Flammability	self-extinguishing according to EN IEC 61386
	Halogenfree	Yes
	Operating Temperature	-58°F to +230°F (-50°C to +110°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	50ft
	Package Quantity (Metric)	15.2m
	Customs Number(Schedule B)	3926909987