

L-10-50R-0-C



Products Low Voltage Products and Systems Installation Products Wire Management and Connectivity Cable Ties

General Information

Extended Product Type:	L-10-50R-0-C
Product ID:	7TAG054750R0009
EAN:	5414363077992
Catalog Description:	CABLE TIE 50LB 12IN UV BLK NYL RLSB
Long Description:	Releasable Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 302mm (11.89 Inches), Width of 7.6mm (0.30 Inches), Thickness of 1.4mm (0.06 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds)

Additional Information

Brand / Label:	CATAMOUNT
Country of Origin:	United States (US)
Customs Tariff Number:	3926909996
Data Sheet, Technical Information:	L-10-50R-0-C
EAN:	5414363077992
ETIM 6:	EC000046 - Cable tie
Instructions and Manuals:	L-10-50R-0-C
Invoice Description:	CABLE TIE 50LB 12IN UV BLK NYL RLSB
Minimum Order Quantity:	100 piece
Package Level 1 EAN:	00728494910000
Package Level 1 Height:	49.53 mm
Package Level 1 Length:	346.71 mm
Package Level 1 Units:	100 piece
Package Level 1 Width:	147.32 mm
Package Level 2 EAN:	50728494910005
Package Level 2 Height:	335.28 mm
Package Level 2 Length:	444.5 mm
Package Level 2 Units:	5000 piece
Package Level 2 Width:	340.36 mm
Product Main Type:	CABLE TIES AND ACCESSORIES
Product Name:	NYLON CABLE TIES
Product Net Weight:	4.536 g
Selling Unit of Measure:	each
UNSPSC:	39121703
UPC:	728494910000



