

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000327](#)
Status: **Active**
Overview: Standard .062" Pin and Socket Power Connectors
Description: 1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Bag

Documents:

Drawing (PDF)	Packaging Specification PK-1190-003 (PDF)
Product Specification PS-1625-010-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	<u>1560</u>
Application	Power
Crimp Quality Equipment	Yes
Overview	<u>Standard .062" Pin and Socket Power Connectors</u>
Packaging Alternative	<u>39-00-0278 (Reel)</u>
Product Name	Standard .062"
UPC	800753330290

Physical


Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	123.700/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.50-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Material Info

Engineering Number	1560TL
--------------------	--------

Reference - Drawing Numbers

Packaging Specification	PK-1190-003
Product Specification	PS-1625-010-001
Sales Drawing	SD-1560-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[1560 Series](#)