



IC PCN FORMAT TEMPLATE

QV DEVICE NAME : LV8548MC

PACKAGE : SOIC10

Test	Specification	Condition	Interval
HTOL	EIAJ ED-4701/100	Tj=Tjmax, Vcc=Operatingmax	1000 hrs
THB*	EIAJ ED-4701/100	85°C, 85% RH, Vcc=recommended	1000 hrs
TC*	EIAJ ED-4701/100	Ta= -65°C to +150°C	100 cyc
AC*	EIAJ ED-4701-3	Ta=121°C ,RH=100% ,205kPa	50 hrs
HTSL	EIAJ ED-4701/200	Ta= 150°C	1000 hrs
RSH	EIAJ ED-4701/300	Ta = 255°C , 10 sec (peak 260°C)	2times

Notes:

The test items with * mark are put into operation after the reflow soldering (at 255°C for 10seconds)

Estimated date for qualification completion: 10 August 2017

List of affected Standard Parts:

Part Number	Qualification Vehicle
LV8548MC-AH	LV8548MC
LV8549MC-AH	