

## Electronic housing - BC 53,6 DKL R KMGY - 2896432

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Installation component housing, Housing cover, Color: light gray, Width: 53.6 mm



### Why buy this product

- Item is from the BC product range
- Conforms to DIN EN 43880
- Tool-free mounting
- Available in overall widths from one to nine width units (17.8 mm ... 161.6 mm)
- Inflammability class V0 according to UL 94
- Variety of connection technologies
- Can be mounted on the DIN rail or the wall
- Optional with bus connector for DIN rail mounting

### Key Commercial Data

Packing unit	10 STK
Minimum order quantity	10 STK
GTIN	 4 046356 103183
GTIN	4046356103183
Weight per Piece (excluding packing)	6.800 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### General

Housing type	Installation component housing
Housing material	Polycarbonate
Color	light gray

#### Ambient conditions

# Electronic housing - BC 53,6 DKL R KMGY - 2896432

## Technical data

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

### Dimensions

Width	53.6 mm
-------	---------

### Technical data

Flammability rating according to UL 94	V0
--	----

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC000886
ETIM 5.0	EC001031
ETIM 6.0	EC001031

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Approvals

### Approvals

# Electronic housing - BC 53,6 DKL R KMGY - 2896432

## Approvals

---

Approvals

UL Recognized / EAC


---

Ex Approvals

---

## Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 240868
---------------	---	---	---------------

EAC		EAC-Zulassung
-----	---	---------------

## Accessories

Accessories

Fiber optics

Component housing - HS LC-V-D3/ R2XC1-5,08 - 2202311



Fiber optics Can be used for the BC housing range (housing must be processed), Color: transparent

---

Component housing - HS LC-V-D3/ R3XC1-5,08 - 2202312



Fiber optics Can be used for the BC housing range (housing must be processed), Color: transparent

---