

ESD Precision Pliers

ESD precision pliers feature a unique joint design that allows the two parts of the pliers to be mated at an earlier stage of the manufacturing process. The resulting perfect alignment delivers a precision fit that eliminates “slack” or “play” and ensures long life with minimal wear.

The extra rigidity and sturdy construction of precision pliers supports our longer jaws and greater taper – ideal for precision work.

Material & Hardness

- AISI 410 Stainless Steel
- 45 Rockwell Hardness (HRC)
- Monocomponent ESD handles



DT000047 - Snipe Nose Head, Smooth Jaws. OAL: 115mm



DT000046 - Tapered Snipe Nose Head, Smooth Jaws. OAL: 115mm



DT000042 - Snipe/Flat Head, Smooth Jaws. OAL: 130mm



DT000039 - Chain Nose Head, Smooth Jaws. OAL: 130mm

DT000040 - Chain Nose Head, Serrated Jaws. OAL: 130mm



DT000033 - Flat Nose Head, Smooth Jaws. OAL: 130mm

DT000034 - Flat Nose Head, Serrated Jaws. OAL: 130mm



DT000044 - Flat Nose Head, Smooth Jaws. OAL: 115mm



DT000035 - Tapered flat Nose Head, Smooth Jaws. OAL: 130mm

DT000036 - Tapered flat Nose Head, Serrated Jaws. OAL: 130mm



DT000037 - Flat Nose Head, Smooth Jaws. OAL: 130mm

DT000038 - Round Nose Head, Serrated Jaws. OAL: 130mm

ESD Precision Pliers



DT000045 - Round Nose Head, Smooth Jaws. OAL: 115mm



DT000041 - Round/Flat Head, Smooth Jaws. OAL: 130mm



DT000043 - Round/Concave Head, Smooth Jaws. OAL: 130mm