

WTHA1 Hot Air Station

Featuring a built-in, high performance hot air pencil

900 W power, compact, easy-operating station with a smart temperature profile mode adjustable for diverse rework applications, assuring fast, safe performance. Up to 100 l / min expanded hot air.



Product picture similar



Features and Benefits

- > Front panel power switch
- > Multi-function LCD screen
- > Quick access menu button
- > Stackable unit
- > 5 Pre-sets / temperature profile
- > Up to 5 pre-sets available
- > Finger-activated switch on hot air pencil
- > Flexible silicone hose

Technical Data

Dimensions L x W x H	210 x 160 x 125 mm 8.30 x 6.30 x 4.90 in
Fuse 120 V (A)	T8 A
Weight	3.0 kg / 6.6 lbs
Power supply	120 V / 60 Hz
Power consumption	900 W
ESD safe	Yes
Temperature range (expanded hot air) l/min 100	50 °C – 600 °C 120 °F – 1100 °F
Temperature accuracy	± 30 °C / ± 54 °F

Order no. Part description

WTHA1 Hot Air Station

WTHA1N WTHA1 HOT AIR STATION, 900 W

Nozzles

T0058768742	TNR 25 ROUND NOZZLE 2.5MM FOR WTHA
T0058768743	TNR 40 ROUND NOZZLE 4MM FOR WTHA
T0058768744	TNR 70 ROUND NOZZLE 7MM FOR WTHA
T0058768745	TNRB 17 ROUND NOZZLE 1.7MM X 45° FOR WTHA
T0058768746	TNRB 60 ROUND NOZZLE 6MM X 45° FOR WTHA
T0058768747	TNA NOZZLE ADAPTER FOR WTHA

Accessories

T0058768762	SILICON PAD FOR WTHA1 PACKED
T0058757898	HOLDER RECLINED FOR HAP 3