

VISION SP-1800 Pair Wall Speakers White(SP-1800)

VISION PAIR OF WHITE WALL LOUDSPEAKERS - 50w (rms) each,Low-impedance,3-way with bass reflex,5.25" woofer,0.5" tweeter,squawker 1",horizontal C brackets included. Dimensions:240 tall ? 178 wide ? 193 deep (mm). ABS Plastic**Lifetime warranty return-to-base,2 years onsite (UK only)**



Vision's SP-1800 professional wall mounted loudspeakers are super-easy to install,look beautiful,and produce rich and powerful sound.

They are 240mm tall and use a 5.25 inch woofer - the most popular size for classroom,meeting room,and boardroom applications.

Key Selling Points

- Three-Way
- Bass Reflex
- Rugged Grille
- Tough Finish
- Pro AV Applications
- Horizontal C bracket

Product Features

Three-Way

These loudspeakers use three drivers;a woofer,a tweeter,and a piezo tweeter. Asking a driver to produce a wide range of frequencies is always a compromise,so dividing the sonic range into three means each driver has a narrower range of frequencies to produce,resulting in less distortion and clearer sound.

Bass Reflex

A bass reflex port allows greater excursion of the woofer,which allows the woofer to produce lower frequencies,and the delayed movement of air from behind the woofer to the front reinforces the bass even more.

Rugged Grille

A metal grille protects the drivers from physical interference.

Tough Finish

Constructed with tough ABS plastic,the finish withstands the rigors of the professional use.

Pro AV Applications

In small to medium presentation environments a wide dispersion is generally more important than microphone feedback management,so no horns are used.

Horizontal C bracket

The adjustable brackets allow the installer to easily angle up 30° or down 30°. Or leave the brackets off and use as shelf speakers.

Main Specifications

Product Description	Vision SP-1800 - speakers - for PA system
Product Type	Speakers - for PA system
System Components	2 speakers
Speaker Type	3-way - passive
Nominal Output Power	50 Watt
Frequency Response	80 - 20000 Hz
Nominal Impedance	8 Ohm
Colour	White
Dimensions (WxDxH)	17.8 cm x 24 cm x 19.3 cm
Weight	4.2 kg
Manufacturer Warranty	Limited lifetime warranty

Extended Specification

General

Product Type	Speakers - for PA system
Features	,Bass Reflex
Enclosure Colour	White
Enclosure Material	ABS plastic

Speaker System

System Components	2 speakers
Speaker Type	3-way - passive
Nominal Output Power	50 Watt
Frequency Response	80 - 20000 Hz
Nominal Impedance	8 Ohm
Sensitivity	89 dB
Recommended Placing	Wall-mountable

Speaker System Details

Driver Details	Speaker: woofer driver - 5.25" Speaker: tweeter driver - 0.5" Speaker: tweeter driver - 1" - piezoelectric
----------------	--

Connections

Connector Type	Speakers input (Binding Post)
----------------	-------------------------------

Miscellaneous

Included Accessories	Wall mounting brackets
----------------------	------------------------

Dimensions &Weight

Width	17.8 cm
Depth	24 cm
Height	19.3 cm
Weight	4.2 kg

Manufacturer Warranty

Service &Support	Limited lifetime warranty
------------------	---------------------------

Product data is provided by CNET,we do not warrant the accuracy and completeness of the material contained in this data sheet