


KEMET Part Number: SS28H-R10450-CH
(UAL28HR10450CH)

Commercial Grade, SS28V/H-CH, 0.045 H



Dimensions

L	30mm MAX
T	30mm MAX
H	24.5mm MAX
S	20mm +/-0.5mm
S1	24mm +/-0.5mm
LL	4mm +/-1mm
F	0.8mm NOM

Packaging Specifications

Weight:	31 g
---------	------

General Information

Style:	Through-Hole Choke
Series:	SS28V/H-CH
Description:	Common Mode Filter
RoHS:	Yes
Miscellaneous:	Inductance Measurement Condition: 1kHz 1V KC530

Specifications

Inductance:	45000 uH
Rated Temperature:	120C
Current:	1 Amps
Voltage AC:	250 VAC
DC Resistance:	650 mOhms
Insulation Resistance:	100 MOhms