


**T-1 Wire Terminal (standard)**



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
CM8798	1.25	.012	.004	1,000	C-6
CM8910	1.35	.220	.020	25,000	C-2R
CM7201	1.50	.015	.010	5,000	C-2R
CM7202	1.50	.066	.015	100,000	C-2R
CM7203	1.50	.075	.030	16,000	C-2R
CM7018	2.50	.320	.210	10,000	C-2R
CM8601	2.50	.015	.001	10,000	C-2R
CM8711	2.50	.320	.210	5,000	C-2R
CM8732	2.50	.100	.100	10,000	C-2R
CM2128	3.0	.013	.001	10,000	C-2R
CM7205	3.0	.015	.020	5,000	C-2R
CM7206	3.0	.024	.020	10,000	C-2F
CM7207	3.0	.060	.030	100,000	C-2R
CM7208	3.0	.120	.150	16,000	C-2R
CM8846	3.0	.008	.001	16,000	C-2R
CM680	5.0	.060	.030	60,000	C-2R
CM683	5.0	.060	.050	25,000	C-2R
CM713	5.0	.075	.090	25,000	C-2R
CM715	5.0	.115	.150	40,000	C-2R
CM3022	5.0	.021	.030	10,000	C-2R
CM3211	5.0	.115	.200	5,000	C-2R
CM6022	5.0	.021	.030	10,000	C-2R
CM6150	5.0	.060	.150	5,000	C-2R
CM6212	5.0	.080	.150	15,000	C-2R
CM6801	5.0	.060	.030	100,000	C-2R
CM6830	5.0	.060	.050	25,000	C-2R
CM6831	5.0	.060	.050	25,000	C-2R
CM7007	5.0	.064	.080	40,000	C-2R
CM7008	5.0	.064	.080	40,000	C-2R
CM7019	5.0	.015	.010	10,000	C-2V
CM7131	5.0	.075	.090	25,000	C-2R
CM7151	5.0	.115	.150	40,000	C-2R
CM7209	5.0	.015	.020	10,000	C-2F
CM7210	5.0	.030	.030	16,000	C-2F
CM7211	5.0	.080	.150	15,000	C-2R
CM7212	5.0	.115	.200	5,000	C-2R
CM7213	5.0	.115	.200	5,000	C-2R