


Flat nut - SACC-E-MU-PG9 - 1504084

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Flat nut with Pg9 thread



Key Commercial Data

Packing unit	100 STK
Minimum order quantity	100 STK
GTIN	 4 017918 833480
GTIN	4017918833480
Weight per Piece (excluding packing)	2.280 g
Custom tariff number	74153300
Country of origin	Germany

Technical data

General

Mounting type	Pg9
---------------	-----

Material

Material, knurls	Nickel-plated brass
------------------	---------------------


Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Flat nut - SACC-E-MU-PG9 - 1504084

Dimensional drawing



Flat nut Pg9

Classifications

eCl@ss

eCl@ss 4.0	23110701
eCl@ss 4.1	23110701
eCl@ss 5.0	23110701
eCl@ss 5.1	23110701
eCl@ss 6.0	23110701
eCl@ss 7.0	23110701
eCl@ss 8.0	23119212
eCl@ss 9.0	23119212

ETIM

ETIM 2.0	EC000129
ETIM 3.0	EC000129
ETIM 4.0	EC000129
ETIM 5.0	EC000129
ETIM 6.0	EC000129

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31161727

Approvals

Approvals

Approvals

EAC

Ex Approvals

Flat nut - SACC-E-MU-PG9 - 1504084

Approvals

Approval details

EAC		EAC-Zulassung
-----	---	---------------
