



Straight bulkhead-push-in connector M-Push 120 brass design nickel-plated

STVS-QSCK-6-MSV-S-M120 push-in bulkhead-connector



230091

<b>Product number</b>	<b>230091</b>
<b>Category</b>	<b>Connection technology / Push-in fittings / Push-in fittings M-Push 120 / Straight push-in fittings/connectors M-Push 120</b>

**Your price:** **2.59 € / Stück**

**Info:**

Date:	<b>2017-07-13</b>
Price unit:	1
Quantity unit:	Stück
Sales unit:	1
quantity min:	1
<b>Old product number</b>	<b>L054.2332, 255041, STVS-QSCK-6-MSV-S-PA-SMQ, 229428, L053.1712, STVS-QSCK-6-MSV-S-SMQ, 256251</b>
DN	4
L max.	7,5
Material of base body	Brass nickel-plated
Material of cartridge	Zinc nickel-plated
Material of lock nut	Brass nickel-plated
Material of releasing ring	POM/PA
Material of tube clamping segment	Stainless steel
Material of tube seal	NBR
Operating pressure	-0,95 - 10 bar
SW	17
Temperature range	-10 °C to +80 °C
Tube-outside-Ø	6 - 6

eClass-5.1

27294201