



Sample photo

Order symbol: PCT 080809
Product nbr: 7022551
Description: Enclosure, PC
Remarks: Clear transparent cover

EAN: 6418074058539
El. number:
Finland: 3435386
Electric No. Denmark: 8212002610
Electric No. Sweden: 7022551

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:			Rating:
mm:	82	80	85
inch:	3.2	3.1	3.3
Materials:			Ingress Protection (EN 60529): IP66/IP67
Material:	Polycarbonate		Impact Resistance (EN 62262): IK07/IK08
Base colour:	RAL 7035 -light grey		Electrical insulation: Totally insulated
Cover screws material:	Stainless steel		Halogen free (DIN/VDE 0472, Part 815): 1
Cover colour:	Clear transparent		UV resistance: UL 508
Gasket material:	Polyurethane		Flammability Rating: UL 746C 5"
Temperatures:			Glow Wire Test (IEC 695-2-1) °C: 960
Temperature °C (short term):	-40 ... 120 °C		NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperature °C (continuous):	-40 ... 80 °C		Certificates:
Temperature °F (short term):	-40 ... 250 °F		SGS Fimko
Temperature °F (continuous):	-40 ... 175 °F		Gost R

EURONORD PC/ABS 82x80x55-95

