

Product availability : Stock - Normally stocked in distribution facility



### Main

Range	Multi 9
Product or component type	OC contact
Device short name	OF
Signal contacts composition	1 C/O
[Ie] rated operational current	3 A at 415 V AC - 50/60 Hz 6 A at <= 240 V AC - 50/60 Hz
[Uc] control circuit voltage	240...415 V AC 50/60 Hz 24...130 V DC
9 mm pitches	1

### Complementary

Range compatibility	Multi 9 GFP GFP Multi 9 C60 C60BP Multi 9 C60 C60BPR Multi 9 C60 C60SP Multi 9 C60H-DC C60H-DC
Mounting mode	Fixed
Mounting support	DIN rail
Height	3.35 in (85 mm)
Width	0.35 in (9 mm)
Depth	2.89 in (73.5 mm)
Product weight	0.07 lb(US) (0.03 kg)
Connections - terminals	Clamp terminal in bottom 1 cable(s) 0 in <sup>2</sup> (2.5 mm <sup>2</sup> ) rigid (AWG 14) Clamp terminal in bottom 2 cable(s) 0 in <sup>2</sup> (1.5 mm <sup>2</sup> ) rigid (AWG 16)
Wire stripping length	0.35 in (9 mm) bottom
Tightening torque	8.85 lbf.in (1 N.m) bottom

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	EN/IEC 60947-5-1 EN 62019-2
Product certifications	CCC CSA UL UR PCT
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

## Ordering and shipping details

Category	00948 - M9 GEN 2 CB UL1077 / IEC
Discount Schedule	DE2
GTIN	00785901759263
Nbr. of units in pkg.	1
Package weight(Lbs)	8.0000000000000002E-2
Returnability	Y
Country of origin	BE